



Collimare®

LED Model Features:

- LED and Cross Hair Lasers on with single momentary button press.
- LED and/or Lasers off with a single momentary button press.
- LED on only (lasers off) with a single button press and hold for 1 second and release the button.
- Lasers on only (LED off) with a single button press and hold until the lasers come on and immediately release the button.
- Programmable LED on time by simply holding the lamp button while applying power to the unit. After 2 seconds the Lasers will flash every second with each flash representing a 15 second interval increase (i.e. Hold and release after 1 flash for 15 seconds, 8 flashes for 2 minutes.).
- Advanced LED control circuitry with proprietary LED direct heat sink surface mounting for high thermal performance, increased output stability and extended life.
- Thermal safety function with indicator (lasers flash every second if overheated until cooled).
- Light field adjustments are accessible without taking the housing off.
- Cross Hair Laser adjustments are accessible without taking the housing off.
- LED light field is very bright (>24 foot candles) and uniform with significantly less edge roll off and high edge contrast ratio (typically around 7:1).
- LED light output is a blue white color spectrum that is highly visible in brighter room conditions.
- Power input (24VDC or 24VAC Isolated). Note: 24VAC must be an isolated supply.
- LED model draws less than 24W (24VDC @ 1A).
- Optional remote lamp input.

13401 W 43rd DR
Unit # 7
Golden, CO 80403
P: 303.278.1496
F: 303.278.1498